


 PRODUCT INFORMATION SHEET (ANNEX 5)		Creation date (dd/mm/yyyy) :		31/10/2022	
		Last update date (dd/mm/yyyy) :		31/10/2022	
1	General information	Supplier's name or trade mark			
2		Supplier's address		ADEO Services, 135 rue Sadi Carnot - CS00001, 59790 RONCHIN	
3		Model Identifier - Luminaire Supplier reference		S220326202WH-4	
4		Light sources maker model		DLB-0895-C	
5		Date of placement on the market		31/10/2022	
6	Type of light source:	Lighting technology used:		LED	
7		Light source cap type (or other electric interface)		connecting leads	
8		Non-directional (NDLS) or directional (DLS):		NDLS	
9		Mains (MLS) or non-mains (NMLS):		NMLS	
10		Connected light source (CLS):		no	
11		Colour-tuneable light source:		no	
12		Envelope:		no	
13		High luminance light source:		no	
14		Anti-glare shield:		no	
15	Dimmable:		no		
16	General product parameters:	Energy consumption in on-mode (kWh/1000 h)		5 kWh/1000h	
17		Energy efficiency class		E	
18		Useful luminous flux (Φ_{use}), indicating if it refers to the flux in a sphere (360°), in a wide cone (120°) or in a narrow cone (90°),		635 360	
19		Correlated colour type		single value	
20		Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K,		4000 K	
21		On-mode power (P_{on}), expressed in W and rounded to the first decimal		4.4 W	
22		Standby power (P_{sb}), expressed in W and rounded to the second decimal		0.00 W	
23		Networked standby power (P_{net}) for CLS, expressed in W and rounded to the second decimal		0.00 W	
24		Colour rendering index, rounded to the nearest integer, or the range of CRI-values that can be set		80	
25		Outer dimensions without separate control gear, lighting control parts and nonlighting control parts, if any (millimetre)			
26		Height (mm)		52.00 mm	
27		Width (mm)		52.00 mm	
28		Depth (mm)		3.50 mm	
29		Spectral power distribution in the range 250 nm to 800 nm, at full-load (insert picture of the spectral power distribution + name of picture+extension (.jpeg))			
30		Claim of equivalent power		-	
31		If yes, equivalent power (W)		W	
32		Chromaticity coordinates (x and y)		X=0.463, Y=0.38	
33		Parameters for directional light sources:	Peak luminous intensity (cd)		cd
34			Beam angle in degrees (no decimal), or the range of beam angles that can be set		Degrees
35	Parameter for LED and OLED light sources:	R9 colour rendering index value		5	
36		Survival factor rounded to the second decimal ($>0.xx$)		0.90	
37		Lumen maintenance factor rounded to the second decimal ($>0.xx$)		0.96	
38	Parameters for LED and OLED mains lights sources:	displacement factor (cos Φ) rounded to the second decimal		0.00	
39		Colour consistency in McAdam ellipses		0.0	
40		Claims that an LED light source replaces a fluorescent light source without integrated ballast of a particular wattage.		-	
41		If yes then replacement claim (W) (no decimal)		0.0 W	
42		Flicker metric (Pst LM) rounded to the first decimal			
43		Stroboscopic effect metric (SVM) rounded to the first decimal			
44	Technical documentation name (in case of light source product)				
45	Light source removing instruction name (in case of containing product)		S220326202WH-4_light source remove instruction.pdf		

		LIGHT SOURCE REMOVING INSTRUCTION		Creation date (dd/mm/yyyy) :	31/10/2022
				Last update date (dd/mm/yyyy) :	31/10/2022
1	General information	Supplier's name or trade mark	INSPIRE		
2		Supplier's address	ADEO Services, 135 rue Sadi Carnot - CS0001, 59790 RONCHIN		
3		Model Identifier - Luminaire Supplier reference	S220326202WH-A		
4		Light sources maker model	DLB-0895-C		

Instructions on how to remove lighting control parts and/or non-lighting parts, if any, or how to switch them off or minimise their power consumption during light source testing

	Explanation of the step	Pictures	Tools
Step 1	remove the plastic shade		By hand
Step 2	Use a flat-blade screwdriver to pull the wires out of the connection terminals		flat-blade screwdriver
Step 3	Use the M8 hexagon nut wrench to unscrew the nut and remove the light source board to be replaced		hexagon nut wrench
Step 4	Replace the light source board with a new light source board, apply an appropriate amount of non-curing thermal grease on the back of the light source board, lock the nut, and insert the wire		By hand
Step 5	Apply an appropriate amount of transparent silicone rubber to the nut and the outlet. Wait 2 hours for the glue to dry, then cover with the plastic shade		By hand
Step 6	Turn on the lamp		By hand
Step 7			